



Versatile new products for multiple applications and specialty conditions



Futura Silver Series Product Catalog



LARGE CAPACITY STAINLESS STEEL



Stainless Steel Models

LAB Model	Cu. Ft Temp Defrost		Defrost	EXT. Doors	Shelves	Width DepthHeight (Exterior)		nHeight	HP	Amps	BTUs	Weight	Shipping Weight
LABH-23-SDSS	23	+4C	Cycle	1 swing	3 adjustable	27	33	83	3/8	6	3200	350	400
LABH-49-SDSS	49	+4C	Cycle	2 swing	6 adjustable	54	33	83	1/2	9	5800	518	560

BULT-IN UNDER COUNTER Perfect for laboratories, satellite pharmacies, stations and patient rooms



Undercounter Refrigerators & Freezers Front Breathing For Built-In Applications

LAB Model	Cu. Ft	Temp	Defrost	EXT. Doors	Shelves	Width (Exteri		nHeight	HP	Amps	BTUs	Weight	Shipping Weight
LABHP-5-URBG	4.6	+4C	Cycle	1 glass swing	2 adjustable	24	23	33	1/3	5	310	97	130
LABHP-5-UFMB	4.5	-20C	Manual	1 solid swing	2 fixed	23.75	23.5	33.5	1/3	5	320	108	140
LABHP-5-URBSS	4.5	+4C	Cycle	1 stainless	2 adjustable	23.75	23.5	33.75	1/3	5	310	100	130
LABHP-5-UFMBS	SS4.2	-20C	Manual	1 stainless	2 fixed	23.75	23.5	33.75	1/3	5	320	100	130

FREESTANDING UNDER COUNTER & COUNTER TOP Perfect for laboratories, satellite pharmacies, surviva stations and natient rooms

nursing stations and patient rooms



Laboratory & Pharmacy Refrigerators

- Temperature Performance:
- Refrigerators: 0°C to 10°C, Preset at 4°C
- Microprocessor Temperature Controller
- Digital Temperature Display
- Audible and Visual Temperature Alarms
- White Powder Coat Paint Exterior
- Heavy Duty Powder Coated Shelves
- Probe Access Port (3/8")
- Optional Remote Alarm Contacts
- Leveling Legs
- Keyed Door Lock
- 120 VAC Operation
- ADA Compliant



Undercounter & Counter Top Refrigerators

Free standing for counter top and under counter areas with adequate space for ventilation

LAB Model	Cu. Ft	Temp	Defrost	EXT. Doors	Shelves	Width (Exteri		Height	HP	Amps	BTUs	Weight	Shipping Weight
LABH-3-URG	2.3	+4C	Cycle	1 glass swing	3 adjustable	17.75	19.25	28.75	1/7	2	310	68	100
LABH-5-URG	5.2	+4C	Cycle	1 glass swing	3 adjustable	23.5	23.75	32.25	1/5	2	310	93	125

FLAMMABLE MATERIAL STORAGE

Flammable Material Storage Laboratory Refrigerators and Freezers

- Meets NFPA and OSHA guidelines for flammable material storage in general laboratory work areas
- UL Listed
- Temperature Performance:

Refrigerators: 0°C to 10°C, Preset at 4°C

Freezers: -18°C to -25°C, Preset at -20°C

Dual Temp: Refrigerator Preset at 4°C

Freezer Preset at -20°C

- Exterior Adjustable Mechanical Thermostat
- 120 VAC Operation with Power Cord
- Leveling Legs
- Keyed Door Lock
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- Durable ABS Material Door Liner
- Probe Access Port (3/8")

Accessories

- Caster Platform
- · Additional Full Shelf



Flammable Material Storage

LAB Model	Cu. Ft	Defrost	Temp	EXT. Doors	INT Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABH-14-RF	14	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	32	60	1/4	4	226
LABH-14-FF	14	Manual	-20C	1 Solid	0	3 Fixed	32	32	60	1/4	4	223
LABH-17-RF	17	Auto	+4C	1 Solid	0	1 Adj/2 Fixed	32	32	65	1/4	4	254
LABH-17-FF	17	Manual	-20C	1 Solid	0	3 Fixed	32	32	65	1/4	4	251
LABH-20-RF	20	Cycle	+4C	1 Solid	0	1 Adj/3 Fixed	32	34	71	1/4	4	306
LABH-20-FF	20	Manual	-20C	1 Solid	0	4 Fixed	32	34	71	1/4	4	303
LABH-30-RF	30	Cycle	+4C	1 Solid	0	5 Adjustable	35	35	72	1/3	7	359
LABH-30-FF	30	Manual	-20C	1 Solid	0	3 Fixed/2 Adj	35	35	72	1/3	7	356
LABH-30-DTF	30	Manual	+4/-20	1 Solid	1	3 Adj Refrig	35	35	72	1/3	7	374





Hazardous Location (Explosion Proof) Laboratory Refrigerators and Freezers

- Meet NFPA and OSHA guidelines for Hazardous Location(s), Class 1, Division II, Group C & D. These units are not intended for use in general clinical or research laboratories.
- UL Listed
- Temperature Performance:

Refrigerators: 0°C to 10°C, Preset at 4°C Freezers: -18°C to -25°C, Preset at -20°C Dual Temp: Refrigerator Preset at 4°C Freezer Preset at -20°C

- Exterior Adjustable Mechanical Thermostat sealed in UL Listed Explosion Proof Box
- Unit Must Be Hard Wired in Conduit to 120 VAC Power Source. Power Cords with Plugs are NOT ACCEPTABLE
- Leveling Legs
- Keyed Door Lock
- Stainless Steel Handle (30 cu. ft. Models only)
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- Durable ABS Material Flat Door Liner
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Additional Full Shelf

Hazardous Location

LAB Model	Cu. Ft	Defrost	Cycle	EXT. Doors	INT Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABH-14-RX	14	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	31	66	1/4	4	238
LABH-14-FX	14	Manual	-20C	1 Solid	0	3 Fixed	32	31	66	1/4	4	235
LABH-17-RX	17	Cycle	+4C	1 Solid	0	1 Adj/2 Fixed	32	31	71	1/4	4	266
LABH-17-FX	17	Manual	-20C	1 Solid	0	3 Fixed	32	31	71	1/4	4	263
LABH-20-RX	20	Cycle	+4C	1 Solid	0	1 Adj/3 Fixed	32	33	77	1/4	4	318
LABH-20-FX	20	Manual	-20C	1 Solid	0	4 Fixed	32	33	77	1/4	4	315
LABH-30-RX	30	Cycle	+4C	1 Solid	0	5 Adjustable	35	34	78	1/3	7	371
LABH-30-FX	30	Manual	-20C	1 Solid	0	3 Fixed/2 Adj	35	34	78	1/3	7	368
LABH-30-DTX	30	Manual	+4/-20	1 Solid	1	3 Adj Refrig	35	34	78	1/3	7	386





DUAL TEMP REFRIGERATORS & FREEZERS

- · Adjustable Mechanical Thermostat
- 120 VAC Operation
- Leveling Legs
- Keyed Door Lock
- Heavy Duty Powder Coated Shelves
- 2 Years Parts and Labor Warranty
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Digital Display

Dual Temp Refrigerators & Freezers

LAB Model	Cu. Ft	Defrost	Temp Ref/Frz		Shelves	WidthDepth Heigh			HP .	Amps	Wgt	Ship
LAB-12-RFCM	8.8 / 3.2	Manual	+4/-12	1/0	3 Adj.1 Fixed Ref / 2 Rem	24	25	63	1/5	1	121	151
LAB-16-RFCM	12.5 / 3.5	Manual	+4/-17	1/	4 Adj. 1 Fixed Ref / 1 Adj	28	26	73	1/5	1.8	158	188
LAB-30-DT	25 / 5	Manual	+4/-20	1/1	3 Adj. Ref	35	35.75	72	1/3	7	358	388

GENERAL

PURPOSE REFRIGERATORS

- Adjustable Mechanical Thermostat
- 120 VAC Operation
- Leveling Legs
- Keyed Door Lock
- Heavy Duty Handle
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- UL Listed
- 2 Years Parts and Labor Warranty
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Digital Display





General Purpose Refrigerators

	-										
LAB Model	Cu. Ft	Defrost	EXT. Doors	Shelves	Width	Deptl	h Height	HP	Amps	Weigh	t Ship Weight
LABH-14-SD	14	Cycle	1 Solid	1 Adj/2 fixed	33.75	28	59	1/3	4	183	213
LABH-17-SD	17	Auto	1 Solid	4 fixed	32	29.5	64.5	1/8	5	214	244
LABH-20-SD	20	Cycle	1 Solid	1 Adj/3 fixed	32	33.75	70	1/4	5	263	293
LABH-30-SD	30	Auto	1 Solid	5 Adjustable	35	34.5	72	1/3	7	395	425
LABH-30-HG	30	Auto	1 Glass	5 Adjustable	36	33.5	72	1/2	9	398	427
LABH-30-HG	C 30	Auto	1 Glass	5 Adjustable	36.5	33.5	72	1/2	9	403	433

^{*}The HGC unit is a chromotography refrigerator

MANUAL

DEFROST PRIME Freezers

- Microprocessor Temperature Controller
- Digital Display with High/Low Temp Alarms
- Audible and Visual Temp Alarms
- Remote Alarm Contacts
- Inner Doors (except FMZ)
- Casters (except FMZ)
- White Baked on Powder Coat Finish
- Heavy Duty Handle
- Keyed Door Lock
- UL Listed
- 120 VAC Operation
- 2 Years Parts and Labor Warranty
- Probe Access Port (3/8")





LAB Model	Cu. Ft	Defrost	Temp	Casters	INT Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABHP-20-FM	20	Manual	-20C	Yes	5	4 Fixed	32	32	77.5	1/4	5	310
LABHP-20-FMZ	20	Manual	-20C	OPT	0	4 Fixed	32	32	77.5	1/4	5	310
LABHP-20-FM3	20	Manual	-30C	Yes	5	4 Fixed	32	32	77.5	1/4	5	330
LABHP-30-FM	30	Manual	-20C	Yes	5	3 Fixed/	35	34.5	79.5	1/3	7	360
						2 Adj						
LABHP-30-FMZ	30	Manual	-20C	OPT	0	3 Fixed/	35	34.5	79.5	1/3	7	360
						2 Adj						
LABHP-30-FM3	30	Manual	-30C	Yes	5	4 Fixed	35	34.5	79.5	1	7	380

MANUAL DEFROST FREEZERS

- Adjustable Mechanical Thermostat
- 120 VAC Operation
- Leveling Legs
- Keyed Door Lock
- Heavy Duty Handle
- White Baked on Powder Coat Finish
- Heavy Duty Powder Coated Shelves
- UL Listed
- 2 Years Parts and Labor Warranty
- Probe Access Port (3/8")

Accessories

- Caster Platform
- Digital Display





General Purpose Freezers

LAB Model	Cu. Ft	Defrost	Temp	EXT. Doors	INT Doors	Shelves	Width	Depth	Height	HP	Amps	Weight
LABH-14-FM	14	Manual	-20C	1 Solid	0	3 Fixed	28	32.5	59	1/4	4	210
LABH-17-FM	17	Manual	-20C	1 Solid	0	3 Fixed	32	29.5	64.5	1/4	4	238
LABH-20-FM	20	Manual	-20C	1 Solid	0	4 Fixed	32	31.5	70	1/4	4	290
LABH-20-FM3	* 20	Manual	-30C	1 Solid	5	4 Fixed	32	31.5	70	1/4	5	315
LABH-30-FM	30	Manual	-20C	1 Solid	0	3 Fixed/2 Adj	35	34	72	1/3	7	343
LABH-30-FM3	* 30	Manual	-30C	1 Solid	5	4 Fixed	35	34	72	1	11	343

^{* -30°}C units come standard with inner doors.



The Futura Family of Cold Storage Products

THE **LAB**RepCo DIFFERENCE:

Guaranteed two-year parts & labor warranty and an additional three-year compressor parts warranty.

Over 30 years experience of delivering quality products to protect and preserve your life's work.

Versatility & variety: from temperature presets to sizes, to shelf configurations, you get the exact products you need.

A support network to assist before, during and after the sale.

For more information contact our Cold Storage Specialsts 1-800-521-0754 / info@labrepco.com www.labrepco.com/coldstorage



